


## tinyTracker 172 nm



Xenon excimer spectra at 172 nm



tinyTracker172

Xenon excimer lamps enable new, resource-saving and more efficient production possibilities. They are used in the field of surface treatment for matting, cleaning, surface activation or to save photoinitiators.

For this purpose, the narrow-band spectrum around 172 nm is usually used to irradiate under inert gas conditions. Then the high photon energy is sufficient to split almost all organic compounds.

The measurement of 172 nm (VUV) is an important component for process control and optimization.


With the tinyTracker 172 we offer a calibrated band radiometer which is suitable for use in an inert atmosphere. The tinyTracker 172 is absolutely calibrated and measures the irradiance and irradiation dose of xenon excimer lamps directly at 172 nm.

Due to its particularly flat design, the tinyTracker172 can be guided through the irradiation channels of UV belt dryers and other industrial equipment. The recording of the values starts automatically when an adjustable minimum irradiance is exceeded. The built-in photodetector is calibrated by PTB. Data is recorded on an exchangeable SD card and transferred via USB to PC.

Evaluation and data export are conveniently performed by the PC Software for tinytracker172. The Li-Ion battery ensures a recording duration of up to 3 hours. The Li-ion battery can be charged directly via the USB interface. An additional power supply unit is included.

## HIGHLIGHTS


- Calibrated photo detector for VUV radiation
- Ideal for the measurement of 172 nm radiation
- Low height of only 10 mm
- Fast data recording with up to 100 measurements per second



Software for tinyTracker172

## TECHNICAL DATA

Measuring range	0-200 mW/cm <sup>2</sup>
Resolution	12 bit
Recording time	up to 3 hours
Sampling frequency	1 - 100 Hz, adjustable
Photo detektor	GAP
Spectral sensitifity	155 nm - 520 nm
Dimensions	195 x 79 x 10 mm
Operating temperature	60 °C
Supply voltage	5 V DC
Power supply	Li-Ion-Akku, 1250mAh
Interface	MiniUSB 2.0
System requirements	Windows 10 / 11 300 MB HDD, 4 GB RAM




Typical, spectral sensitivy of the photo detector

## PART NUMBERS

tinyTracker 172	824204
-----------------	--------

## SCOPE OF DELIVERY

tinyTracker172, manufacturers certificate of calibration, USB cable, wall plug adapter, carrying case



Software for tinyTracker172

